


# 5710 microtec



Zrno:  
karbid křemíku

100 $\mu$	
80 $\mu$	
<b>60 <math>\mu</math></b>	●
50 $\mu$	
45 $\mu$	
<b>40 <math>\mu</math></b>	●
<b>30 <math>\mu</math></b>	●
20 $\mu$	
15 $\mu$	
<b>12 <math>\mu</math></b>	●
<b>9 <math>\mu</math></b>	●
6 $\mu$	
<b>5 <math>\mu</math></b>	●
<b>3 <math>\mu</math></b>	●
1 $\mu$	
0,5 $\mu$	
0,1 $\mu$	



100 $\mu$	
80 $\mu$	
<b>60 <math>\mu</math></b>	●
50 $\mu$	
45 $\mu$	
<b>40 <math>\mu</math></b>	●
<b>30 <math>\mu</math></b>	●
20 $\mu$	
15 $\mu$	
<b>12 <math>\mu</math></b>	●
<b>9 <math>\mu</math></b>	●
6 $\mu$	
<b>5 <math>\mu</math></b>	●
<b>3 <math>\mu</math></b>	●
1 $\mu$	
0,5 $\mu$	
0,1 $\mu$	

holý  
SKF

Posyp:  
speciální, lesklý



Podklad:  
speciální fólie 75  $\mu\text{m}$

