

5900 microtec




Zrno:
korund



holý

100 μ	
80 μ	
60 μ	●
50 μ	●
45 μ	
40 μ	●
30 μ	●
20 μ	●
15 μ	●
12 μ	
9 μ	●
6 μ	
5 μ	
3 μ	
1 μ	
0,5 μ	
0,1 μ	



100 μ	
80 μ	
60 μ	●
50 μ	●
45 μ	
40 μ	●
30 μ	●
20 μ	●
15 μ	●
12 μ	
9 μ	●
6 μ	
5 μ	
3 μ	
1 μ	
0,5 μ	
0,1 μ	

Posyp:
elektrostaticky nanesený



Podklad:
speciální fólie 75 μ m

